# **COVENTRY**<sup>TM</sup> Clean Room Products

Division of ITW Chemtronics ®

#### TDS # 51125F

### Wrapped Polyester Swabs for Fiber Optics

#### **PRODUCT DESCRIPTION**

**Coventry<sup>TM</sup> Wrapped Polyester Swabs** consist of 100% continuous monofilament, cleanroom, polyester knit fabric held in place using a fluoropolymer shrink tube. These swabs are low in nonvolatile residue, ionic and particulate contamination, while providing exceptional strength and solvent resistance. The are characterized by the following features:

- No edge seamless head design eliminates seams and reduces scratch potential
- 'Pillow-Tipped' design provides high solvent capacity and cushioning for delicate parts
- High strength , durable head
- Low particulate and nonvolatile residue contamination
- No adhesives or binders are used in the construction
- Excellent solvent compatibility

#### **TYPICAL APPLICATIONS**

- Designed to clean fusion splice mirrors
- Replaces cotton tip swabs with fiber free design
- Replaces wood handled swabs with cleanroom compatible material
- Micro Mechanical Cleaning

#### COMPATIBILITY

<u>Polyester Fabric Heads</u> are compatible with most common solvents such as aliphatic solvents, isopropyl alcohol, methyl alcohol, dilute or weak acids, and ketones such as acetone or MEK.

<u>Glass Filled Nylon Handles</u> are stiff for physical stoutness and resistance to most chemical solvents.

#### AVAILABILITY

51125F 2.75 " (7.1 cm) Glass Filled Nylon Handle, 0.23" (5.90 mm) ) Wrapped Polyester Head, 15 swabs/ tube 18 tubes/case

#### Available as EFB-12

#### MANUFACTURED BY:

COVENTRY<sup>™</sup> Clean Room Products Division of ITW Chemtronics<sup>®</sup> 8125 Cobb Center Drive Kennesaw, GA 30152 USA 1-770-424-4888

REV. (01/06)

### **TECHNICAL HOT LINE 1-800-TECH-401**

### Wrapped Polyester Swabs for Fiber Optics

Head		
Material	Wrapped Polyester Knit Fabric	
Swabs:	51125F (EFB-12)	
Head	0.23"	
Diameter	(5.7 mm)	
Handle	2.80"	
Length	(7.1 cm)	
Particle Counts:		
0.5 - 1 um	3,463	
1.0 - 2 um	1,605	
2.0 - 5 um	206	
5.0 - 10 um	29	
10 - 25 um	14	
over 25 um	23	
TOTAL	5,340	
NVR		
(ug/swab)	none detected	
Chlorides		
(ug/swab)	3	

The swabs were tested by Particle Measurement Technology. All tests were done using the recommended practices of the Institute of Environmental Science, Swabs and Wipes Working Group.

# TECHNICAL AND APPLICATION ASSISTANCE

Coventry<sup>™</sup> Clean Room Products provides A technical hotline to answer your technical And application related questions. The toll free number is: **1-800-TECH-401** 

**DISTRIBUTED BY:** 

Chemtronics® is a registered trademark of ITW Chemtronics. All rights reserved. Coventry<sup>™</sup> and Aqua-Prime<sup>™</sup> are trademarks of ITW Chemtronics. All rights reserved.

## **TECHNICAL HOT LINE 1-800-TECH-401**